

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
After Process	Yes, this material will work with this application
Application	General & Industrial Identification
Approval/Compliance	UL Recognised; CSA Accepted; Halogen Free (DIN VDE 0472/part 815)
Article No.	114805
Board Application	Through Hole - Top
Brady Material No.	B-428
Material Type	Metallised Polyester
Brand	MetaLabel™ Series
Colour	Green on Silver
Finish	Matt
Description	Labels for the BMP™71 Label Printer. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Service Temp. °C	120
Order Reference	M71-30-428-CALI
Printable Area - Height (mm)	12.70
Printer Compatibility	BMP71
Ribbon Series	M71-R4300
Shape	Rectangle
Size - Height (mm)	19.05
Size - Width (mm)	38.10
Surface Mount Technology SMT	No, this material does not work with this application
Through Hole Technology	Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No
Total Qty per Pack	250 Label(s) / Box
Vertical Repeat (mm)	22.23

Industry	Facility & Safety Identification;General Industry;Manufacturing;Process
Language Support	English
Min. Service Temp. °C	-40
Printable Area - Width (mm)	38.10
QTY. per Row	1
Thickness (mm)	0.112
Legend	CALIBRATION