

Datasheet

IEC C13 12 Gang Distribution Unit, 20A, 250 V

RS Stock number 472-6453



Product features

- Each output is individually fused and has associated power availability / fuse failure indication.
- Options of single or dual input. The dual input version allows for standby supply. In the event of failure of the primary supply, the unit will switch over to standby supply.
- Number of contacts 12
- Sequenced or non sequence
- Front panel control option – paddle switch
- Maximum total load 20 amps
- 220/230 AC operation
- Max load on any output 6 amps

MATERIALS

BODY	= 316 STAINLESS STEEL
STEM	= 316 STAINLESS STEEL
STEM SEAL	= PTFE
BALL SEAL	= PTFE/PVDF
TEMP. RANGE	= -40 TO +200°C
LEVER	= 316 STAINLESS STEEL (WITH PLASTIC COVER)