



HIGH PROTECTION RIGID CASES COMPOSITIONS

■ 4750RCHDW01FF1

240 PCS

- Aviation Mechanics, especially for mobile application
- Hardware: 4750RCHDW01. Heavy Duty Rigid Case with wheels
- Metric & inch
- Sizes: 1/4; 3/8



ERGO TOOL MANAGEMENT SYSTEM



FF2B01 - 61 pcs

A6700DZ SOCKETS 1/4", BI-HEX, AEROSPACE SHORT SERIES
3/16", 7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16"

A6800DZ SOCKETS 1/4", BI-HEX, AEROSPACE LONG SERIES
3/16", 7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16"

6950SL REVERSIBLE RATCHET 1/4", SLIMHEAD

6954 T-HANDLE 1/4"

6956 SPINNER HANDLE 1/4"

6958 BREAKER BAR 1/4"

6960 / 6961 EXTENSION BARS 1/4"

50, 100 mm

6962L EXTENSION BAR 1/4"

355 mm

6966 UNIVERSAL JOINT 1/4"

7764 ADAPTOR F 3/8" - M 1/4"

7765 ADAPTOR F 1/4" - M 3/8"

6972H BIT HOLDER 1/4"

A7402DZ SOCKETS 3/8", BI-HEX, LONG SERIES, AEROSPACE
1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 19/32", 5/8", 11/16", 3/4"

A7400DZ SOCKETS 3/8", AEROSPACE SHORT SERIES
1/4", 5/16", 3/8", 7/16", 1/2", 17/32", 9/16", 19/32", 5/8", 11/16", 3/4"

7750SL RATCHET 3/8" SLIMHEAD

7752 SPEEDER 3/8"

7760 / 7761 / 7762 EXTENSION BARS 3/8"

75, 125, 250 mm

7766 UNIVERSAL JOINT 3/8"

8164-1/2 ADAPTOR F 3/8" - M 1/2"

7407H SOCKET HOLDER 3/8"

1/4" - 3/8"

S6106KA SPARK PLUG SOCKET 7/8"



FF2B02 - 69 pcs

A6700DM SOCKETS 1/4", BI-HEX, AEROSPACE SHORT SERIES
5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14

A6800DM SOCKETS 1/4", AEROSPACE LONG SERIES
4.5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14

A7400DM SOCKETS 3/8", BI-HEX, AEROSPACE SHORT SERIES
10, 11, 12, 13, 14, 15, 16, 17, 18, 19

A7402DM SOCKETS 3/8", BI-HEX, LONG SERIES, AEROSPACE

10, 11, 12, 13, 14, 15, 16, 17, 18, 19

4020L-M LILIPUT COMBINATION WRENCH

5, 5.5 mm

111M COMBINATION WRENCHES

6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 22, 24

BE-9770 BLACK HEX KEYS SET, LONG BALL END, 9 PCS

1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm



FF2B03 - 44 pcs

A6710DZ SWIVEL SOCKETS 1/4",
BI-HEX, AEROSPACE

3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16

A6710DM-7 SWIVEL SOCKETS 1/4",
BI-HEX, AEROSPACE

7 mm

2058-BR BIT-RATCHET 1/4"

7 mm

1950MZ-3/8 CROWFOOT ADJUSTABLE WRENCH 3/8"

BE-9780 BLACK HEX KEYS SET,

LONG BALL END, 12 PCS

0.050", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16",

7/32", 1/4", 5/16"

111Z COMBINATION WRENCHES

1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4",

13/16", 7/8", 1"

1320RZ RATCHETING RING WRENCHES

1/4X5/16", 5/16X11/32", 3/8X7/16", 1/2X9/16"

1931Z LILIPUT DOUBLE OPEN-END WRENCHES

3/16", 7/32", 1/4"



HIGH PROTECTION RIGID CASES COMPOSITIONS

■ 475ORCHDW01FF1

240 PCS

- Aviation Mechanics, especially for mobile application
- Hardware: 475ORCHDW01. Heavy Duty Rigid Case with wheels
- Metric & inch
- Sizes: 1/4; 3/8



ERGO TOOL MANAGEMENT SYSTEM



FF2B04 - 45 pcs

9070C ADJUSTABLE WRENCH CHROMED 6" ERGO™

158x20 mm

2509 FLEXIBLE PICK-UP TOOL

525 mm

808050 RATCHETING BIT SCREWDRIVER

59/S28-4 BITS SET FOR SLOTTED, PHILLIPS, TORX®,
HEXAGON AND TORQ-SET® HEAD SCREWS

28 PCS

701 PRECISION SCREWDRIVERS FOR PHILLIPS HEAD
SCREWS

PH00X50, PH0X50

700 PRECISION SCREWDRIVERS HEAD SCREWS, SLOTTED

1.5X50, 1X50

BE-8020L / BE-8040 SCREWDRIVERS ERGO™, SLOTTED

0.5X3X75, 0.8X4.0X100

BE-8150 / BE-8255 SCREWDRIVERS ERGO™ SLOTTED

1.0X5.5X100, 1.2X6.5X115

BE-8610 / BE-8620 SCREWDRIVERS ERGO™ PHILLIPS

PH1X75, PH2X100

BE-8080-10 SCREWDRIVER

TORQ-SET, ERGO™

10X100

2535F2 MAGNETIC PICK-UP TOOL

1 kg

5516 GENERAL PURPOSE TWEEZER

150 mm

1544 FEELER GAUGE



FF2B05 - 15 pcs

5515T-52 TELESCOPIC SWIVEL HEAD MIRROR

Ø 50mm

2650 SLIP JOINT, CONNECTOR PLIER

2855 WIRE TWISTING PLIER

224 mm

4130 SIDE CUTTING PLIER, ERGO™

120 mm

2101GC SIDE CUTTING PLIER, ERGO™

125 mm, 160mm

2427 GC-200IP LONG, ROUND NOSE CHROMED PLIER,
ERGO™

160 mm

2628 GC-160IP COMBINATION PLIER, CHROMED, ERGO™

160 mm

8224CIP SLIP JOINT PLIER, ERGO™

4830 FINE MECHANICAL SNIPER NOSE PLIER, ERGO™

2820EF2 ELECTRICIAN'S KNIFE

200 mm

BFLA01 Q3 LED-TORCH

MTB-3-16-E MEASURING TAPE

3 m

1150-1/2H/P CALIPER

150 mm

1179-FLX-2 FLEXIBLE MEASURING ROD

300 mm



FF2B06 - 6 pcs

3625N-32 PLASTIC HAMMER

481-300 DIN HAMMER

300 mm

3734 DRIFT PUNCHES

Ø 3, 5, 8 mm

3735-5-120 CENTRE PUNCH

5X120 mm