

Datasheet

RS Pro On/Off Temperature Controller, 48 x 48mm, J Type Thermocouple Input, 230 V ac Supply

RS Stock No: **875-1220**



Product Details

RS Pro on/off temperature controller measuring 48 x 48 mm works with type J thermocouple input using 230 V ac supply. These temperature controllers are designed for measuring and controlling temperature. They can be used in many applications with their on/off control form, heating and cooling control form and easy-use properties.

Features and Benefits

- 3 digits display
- On/Off control form
- Selectable heating and cooling function
- Operating type selection with hysteresis
- Adjustment of temperature offset value
- Minimum pulling time adjustment for control outputs
- Password protection for programming mode

**Specifications:**

Input Type	J Type Thermocouple
IP Rating	NEMA 4X
Maximum Operating Temperature	+50°C
Minimum Operating Temperature	0°C
Mounting Type	1/16 DIN Rail
Number of Inputs	1
Number of Outputs	1
Output Type	Relay
Panel Depth	95 mm
Size	48 x 48 mm
Supply Voltage	230 V ac
Termination Type	Screw
Panel Cut Out Size	46 x 46 mm