

RS Part Number: **773-7960** Specifications and dimensions



- Boxed isolator 4 pole
- ABS plastic enclosure with padlockable handle
- Oversized enclosure to facilitate wiring

Specifications	
Height	175 mm
Width	125 mm
Depth	90 mm
Depth including switch	134 mm
Degree of protection	IP65
Rated operational current Ie AC21A	25 A
Rated operational current Ie AC22A	20 A
Rated operational voltage Ue IEC & EN	690 V
Rated operational power AC23A 380-440V	11 kW
Rated operational power AC3 440V	7.5 kW
Maximum gL fuse size IEC	20 A
Rated fused short circuit capacity IEC	5 kA
Knockout size	20 mm
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	6 mm ²
Recommended tightening torque	1.7 Nm
Number of possible auxilliary contacts	1
Related products	
Neutral contact (early make/late break)	136-5280