



Coded projection keyboard - Tercode 2008

Reference: 004255

Quick Overview

-

Product Description

Specially designed for access control offices - protrude polycarbonate housing - gray color - Buttons glow - codes 8 - 2 relays

Programming directly from the keypad, protected by a master code interchangeable

- Memory storage for data backup.
- Power supply: 12 V DC or AC
- Power consumption: Standby: 5 mA, maximum 80 mA DC / 160 mA alt
- Dimensions: 77 x 56 x 24 mm
- 3 LEDs indicating the front
- Protection class: IP 43
- Operating temperature: -20 ° C to +50 ° C
- Keypad lock for 30 seconds after six successive false codes
- Inputs: 8 code words spread over 5 2 relays, 4 codes on the relay 1 (green LED), 4 codes on relay 2 (red LED), a master code at 5 words
- Outputs: monostable or bistable, 2 contacts NO-NC - 2A - 24 V, 1 NC contact retention clips or disassembly
- Timers: 1 to 99 seconds