

Datasheet

RS Pro Spiral Wrap 9mm 32mm polyethylene (PE)

RS Stock No: **227-980**



Product Details

RS Pro spiral wrap in natural colour, is made of PE. It has internal diameter of 9 mm, maximum bundle diameter of 32 mm, maximum cable diameter of 32 mm, wall thickness of 0.85 mm and 3 m long. A pre-formed flexible PE spiral wrapping can be expanded by wrapping around cables forms, providing both protection and organisation of cables. Lead-outs allow cables to branch out at any point. A quick, effective system is capable of continuous adjustment or re-use. The operating temperature range is from -50 to +50 deg C.

Features and Benefits

- 3 m long
- Used for organising and protecting cables and hoses
- Easily applied to electrical harnesses, cables and wire bundles
- Flexible and durable
- Reusable
- Comes in natural colour
- Made from PE

**Specifications:**

Cable Diameter Range	9 to 32 mm
Colour	Natural
Internal Diameter	10.3 mm
Length	3 m
Material	PE
Maximum Cable Diameter	32 mm
Maximum Operating Temperature	+50°C
Minimum Cable Diameter	9 mm
Minimum Operating Temperature	-50°C
Operating Temperature Range	-50 to +50°C
Wall Thickness	0.85 mm
Outer Diameter	12 mm
Width	15 mm