

## Cable protection end sleeve - WP-SC BRASS 14 - 3241066

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




End sleeves as cable protection, made of brass

Image shows WP-TS BRASS 14 version



### Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 711883
Weight per Piece (excluding packing)	2.97 g
Custom tariff number	74122000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Diameter	14.00 mm
----------	----------

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 250 °C
---------------------------------	-------------------

#### General

Color	Brass
Components	Halogen-free
Material	Brass

### Classifications

#### eCl@ss

eCl@ss 4.0	27141209
------------	----------

## Cable protection end sleeve - WP-SC BRASS 14 - 3241066

### Classifications

#### eCl@ss

eCl@ss 4.1	27141209
eCl@ss 5.0	21132007
eCl@ss 5.1	21132007
eCl@ss 6.0	21132007
eCl@ss 7.0	27439210

#### ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC000519

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

### Accessories

#### Accessories

##### Corrugated pipe

##### Protective hose - WP-STEEL ZC 14 - 3240865



Galvanized steel protective hose, 1 Pcs. / Pkt. = roll à 10 m

---

##### Protective hose - WP-STEEL S 14 - 3240687



Stainless steel protective hose, 1 Pcs. / Pkt. = roll à 10 m