






AMP WIRE RANGE	 Listed
6 AWG SOLID OR STRANDED	NOT APPLICABLE
 LR7189 Certified	MILITARY P/N AND CLASS
NOT APPLICABLE	NOT APPLICABLE

 STAMP AMP 6* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 343° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		WIRE CROSS SECTIONAL AREA RANGE: 10.5-16.8MM ² [20,800-33,100] CIR MILS SOLID OR STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
FOR ORDER ENTRY	1-800-526-5142	

				PART NO									
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN TA BRINKMAN 3-24-93		 TE Connectivity							
				CHK DA PATTERSON 3-24-93									
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DE MILLER 3-24-93		NAME							
		0 PLC ± -		PRODUCT SPEC		TERMINAL, RING TONGUE, HEAT RESISTANT, STRATO-THERM TM							
		1 PLC ± -		—									
		2 PLC ± -		APPLICATION SPEC									
		3 PLC ± -		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		4 PLC ± -		—		A2		00779		C-323170		—	
MATERIAL		FINISH		WEIGHT									
COPPER PER ASTM B-152 ANNEALED		NICKEL PLATE 0.00762[.000300] MIN THK PER QQ-N-290		—		CUSTOMER DRAWING		SCALE		4:1		SHEET 1 of 1 REV F1	