

Datasheet

RS 15 Core Screened Industrial Cable, PVC Sheath, 5.2mm OD, 0.055 mm² CSA 0.25 A, 300 V, 25m
Stock Number - 660-0401



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):300

Flammability Test: IEC60332-1



ENGLISH

Construction:

Conductor: Tinned Copper

Conductor Dia. (mm): 0.10 ± 0.008 x 7

Insulation: PVC

Insulation Dia. (mm): 0.7 ± 0.05 x 15C

Tape: Mylar Spiral

Coverage: $\geq 115\%$

Braid Shield : Tinned Copper

Conductor Dia. (mm): 0.15

Conductor Qty: 16x6

Pitch(mm):

Coverage : 91%

ID Thread : Green, White/Green

A rip cord : 500 D

Jacket: FR-PVC

Outer Dia. (mm): 5.2 ± 0.15

Colour:

**The colour of the insulation: Red , Blue , Green ,
Yellow ,**

**White , Black , Brown , Violet , Orange , Pink , Light
Green ,**

Grey , Red/Blue , Green/Red , Yellow/Red

The jacket colour: Black

Electrical Characteristics:

Max.Conductor DC Resistance at 20°C (Ω /Km) :

<345

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :

>200

Current Rating : 0.25 A

