








NO	DESCRIPTION	DATE
①	ADD MIS PART NO.	04.01.04'
②	ADD A-A SECTION $\phi 2.7 \rightarrow \phi 2.7^{+0.1}_0$	12.02.04'
③	ADD (P/N:544-4382)	04.14.10'
④	3.0 $\rightarrow$ 2.8	06.28.10



△ A-A SECTION



△ MIS PART NO: □69-0025H-01 (P/N:544-4382) △

APPROVED

by _____ DATE: _____

6	SPRING	IRON	1	ZINC
5	SCREW	IRON	2	ZINC
4	SCREW	IRON	2	ZINC
3	SCREW	IRON	2	ZINC
2	CAP	ABS	1	NONE
1	BODY	ABS	1	NONE
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



DESCRIPTION		25PIN D-HOOD-1			
製圖	DRAWN	Yoko	TOLERANCE	品名	25PIN D-HOOD-1
	CHECK			TITLE	\ROHS COMPLIANT
檢圖	Angela	XXX	±0.05	單位	UNIT
	APPROVAL			mm(in)	DWG.NO. 55-0082
認定	Angela	ANGLE	±5°	比例	SCALE
				2:1	

DATE	版次	REV.
10.30.96'	A-4	