

Datasheet

Art.No. 92.232.3000.2

Cable assembly GST18i3K1BS 15 30WS

Extension cable, female - male, length 3m, GST18i3, 3 pole, 250 V, 16 A, cable type H05VV, cross section 1,5 mm², colour of coding: white, colour of cable: white



Art.No.	92.232.3000.2
EAN	4015573323452
Order unit	25 pieces

Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	White
Marking of poles	
Color of housing inclusive strain relief	White

Model

Number of poles	3
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Cable type	H05VV-F
Cable colour	White
Cable diameter	8.3 mm
Version of cable	Female - male
Version cable end 1	female
Version cable end 2	male

Material

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	3 m
--------------	-----



Drawings

Buchse/female connector Steckerteil/male connector

Gesamtlänge / totale length

Kabel/cable H05VV-F3G1,5
Farbe/colour: siehe Tabelle/see table

Weitere Daten siehe Katalog
further data see catalog

.F	Farbe colour	Codierung *X* Buchse female	Codierung *Y* Stecker male	Kabelfarbe cable colour
.1	schwarz black	N PE L	L PE N	schwarz black
.2	weiß white	N PE L	L PE N	weiß white
.3	grau grey	N PE L	L PE N	schwarz black
.5	rot red	N PE L	L PE N	schwarz black

Teile-Nr. part-no.	L	Beispiel (Farbe: schwarz) example (colour: black)	Typ type
92.232.XX00.F	XX in dm-Schritten	92.232.1000.1 = 10dm/L= 1000mm	GST1813K1BS 15 10SW
U2.232.XX00.F	XX in m-Schritten	U2.232.1200.1 = 12 m/L=12000mm	GST1813K1BS 15 X12SW

SW = schwarz/black
WS = weiß/white
GR01 = grau/grey
RT03 = rot/red

Typ/type: GST1813K1BS 15

92.232.0200.1 01K

INSTALL. COUPLER
KONFEKTLEITUNG

Buchse/female - Stecker/male 1,5mm
Crimpauführung/crimper version K1 250V

DU-PEM-08-94