

Datasheet

RS Pro 2A Radial Non-Resettable Wire Ended Fuse, 250 V

RS Stock No: **767-5128**



Product Details

RS Pro radial non-resettable fuse withstands currents up to 2 A and voltages up to 250 V. It has thermoplastic body for added durability. This fast acting fuse forms a convenient and reliable solution to a vast array of application requirements.

Features and Benefits

- Fast acting fuse
- Non-resettable
- Radial fuse
- Wire-ended

**Specifications:**

| | |
|---|------------------------------|
| Body Height | 7.7 mm |
| Body Length | 8.35 mm |
| Body Material | Thermoplastic |
| Body Width | 4.3 mm |
| Breaking Capacity (at Maximum Voltage Rating) | 35 A at 250 V ac |
| Current Rating | 2 A |
| Lead Orientation | Radial |
| Maximum Operating Temperature | +125°C |
| Minimum Operating Temperature | -55°C |
| Voltage Rating | 250 V |
| Voltage Rating | 250 V |
| Wire Diameter | 0.62 mm |
| Wire Length | 22 mm, 4.3 mm |
| Wire Pitch | 5.08 mm |
| Fuse Type | Fast Acting |
| Nominal Resistance | 0.033 Ω |
| Standards Met | VDE, CSA, UL, PSE, CCC, RoHS |