

Cover profile - CD-HF COVER 30 - 3240370

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cover for cable duct, light gray, halogen-free, width: 30 mm, length: 2000 mm

The illustration shows the version in gray



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 508551
Weight per Piece (excluding packing)	0.18 g
Custom tariff number	39259020
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	2000 mm
Height	14.4 mm
Width (a)	30 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

General

Color	light grey RAL 7035
Components	Halogen-free
Inflammability class according to UL 94	V0
Material	PC/ABS

Cover profile - CD-HF COVER 30 - 3240370

Classifications

eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602
eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400776
eCl@ss 8.0	27400776

ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000727
ETIM 5.0	EC000727

UNSPSC

UNSPSC 6.01	30101815
UNSPSC 7.0901	30101815
UNSPSC 11	30101815
UNSPSC 12.01	30101815
UNSPSC 13.2	30101815

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approvals submitted

Approval details

VDE Zeichengenehmigung
