








- NOTES:
- MATERIAL:
HOUSING: THERMOPLASTIC WITH 30% GF, UL 94V-0, COLOR: (SEE TABLE).
CONTACTS: PHOSPHOR BRONZE, THICKNESS=0.25mm..
SHIELD: BRASS, THICKNESS=0.30mm.
 - FINISH:
CONTACT: 0.762μm [30μ"] MIN. GOLD PLATED ON CONTACT AREA.
3.048μm [120μ"] MIN. BRIGHT-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
SHIELD: 0.762μm [30μ"] MIN. NICKEL OVER 0.762μm [30μ"] MIN.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE CONNECTIVITY TEST SPEC. 109-201, CONDITION B.




RECOMMENDED P.C.B. LAYOUT (THICKNESS=1.6mm)
(TOP VIEW) TOLERANCES: ±0.05



w/	BLACK	1-1734082-2
	WHITE	1-1734082-1
w/o	BLACK	1734082-2
	WHITE	1734082-1
POST	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 200CT2005	TE Connectivity		
		CHK S. HSU 200CT2005			
DIMENSIONS: MM		APVD W.J. KE 200CT2005	NAME		
		PRODUCT SPEC 108-57505	USB CON, RCPT, ASS'Y, R/A SMT, A TYPE		
		APPLICATION SPEC 501-57579			
MATERIAL SEE NOTE		WEIGHT 1.82 GRAMS	SIZE A3	CAGE CODE 00779	DRAWING NO C=1734082
SEE NOTE		CUSTOMER DRAWING			RESTRICTED TO -
		SCALE -	SHEET 1 OF 4	REV B1	



LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
		SEE SHEET 1.						

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.35

2 PLC ± 0.25

3 PLC ± 0.15

4 PLC ± -

ANGLES ± 3°

FINISH

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

USB CON, RCPT, ASS'Y, R/A SMT, A TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1734082

SCALE

SHEET

REV



-


2 OF 4

B1

2-1734082-1

PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity	
DIMENSIONS: MM		CHK			
		APVD		NAME USB CON, RCPT, ASS'Y, R/A SMT, A TYPE	
		PRODUCT SPEC			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO A3 00779 C-1734082 -	
MATERIAL		WEIGHT			
FINISH		CUSTOMER DRAWING		SCALE	SHEET 3 OF 4
					REV B1

