






LOC	QTY	REV	DATE	BY	CHK	APPV
CM	53					
REVISIONS						
REV	DATE	DESCRIPTION	BY	CHK	APPV	REV
E	11-19-97	REV & REDWN PER EC 0L30-0248-97				R5

AMP LOGO AND CAVITY NUMBERS LOCATED ON EITHER SURFACE, OPPOSITE SIDE OPTIONAL.




RECOMMENDED CUT OUT
FOR 1.58 MAX THICK PANEL



3-DIMENSIONAL MODEL
NTS

6.53	.257	35.10	1.382
6.35	.250	27.94	1.100
1.58	.062	25.96	1.022
0.76	.030	21.89	.862
0.51	.020	19.48	.767
0.25	.010	9.27	.365
0.13	.005	8.89	.350
MM	IN	MM	IN
CONVERSION TABLE			



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN K. WHITAKER 11-19-97	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK R. SWING 11-19-97	NAME PLUG PANEL MOUNT, 3 CIRCUIT, .250 PIN AND SOCKET	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.01 1 PLC ±.01 2 PLC ±0.13 3 PLC ±.01 4 PLC ±.01 ANGLES		APVD K. COBLE 11-19-97	RESTRICTED TO -	
MATERIAL NYLON, JL 94V-2, NATURAL		FINISH -	HEIGHT -	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1