





NOTES

- 1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, UL94V-0
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- 2. FINISH (CONTACT AREA): 0.38μm MIN GOLD PLATING OVER Ni PLATING
- 3. FINISH (CONTACT AREA): 0.76μm MIN GOLD PLATING OVER Ni PLATING
- 4. FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
- 5. FINISH (RETENTION LEG): TIN-LEAD PLATED (CONTACT TAIL) OVER NICKEL
- 6. FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

注記

- 1. 材料: ハウジング: ガラス入り熱可塑性樹脂, UL94V-0
コンタクト: 銅合金
リテンションレグ: 銅合金
- 2. めっき: コンタクト接触部: ニッケル下地の上に金めっき 0.38μm MIN
- 3. めっき: コンタクト接触部: ニッケル下地の上に金めっき 0.76μm MIN
- 4. めっき: コンタクト: 全面Ni下地
接触部: 2.0 μm MIN スズめっき
- 5. めっき: リテンションレグとコンタクト半田付部
ニッケル下地の上に半田めっき
- 6. めっき: リテンションレグとコンタクト半田付部
ニッケル下地の上にスズめっき

△6 △4	↑	-5
△6 △3		-3
△6 △2		316517-2
FINISH	型番	PART NUMBER

Copyright ©1995 年 AMP (Japan), LTD. ALL RIGHTS RESERVED.				Copyright ©1995 年 AMP (Japan), LTD. ALL RIGHTS RESERVED.				tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan			
B REVISED (FJD0-0039-03) TS J.M. 8/2				A REVISED (FJD0-0114-03) TS SM 10/24				O RELEASED FJ00-3261-95 NM Y.I. 10/24			
LTR 変更 (REVISION RECORD)				DR CHK DATE				CHK. Y.ISHIKAWA			
WIRE RANGE				INSULATION DIA				NAME (NAME)			
mm (AWG)				mm				DYNAMIC (D-3500) 20 POS. V HDR. ASS'Y			
MATERIAL (SEE NOTE)				FINISH (SEE NOTE)				GENERAL TOLERANCE			
24 OCT 95 N.MATSUBARA				24 OCT 95 N.MATSUBARA				10mm ±0.35			
24 OCT 95 Y.ISHIKAWA				24 OCT 95 S.MANABE				10mm ±0.4			
24 OCT 95 Y.ISHIKAWA				24 OCT 95 S.MANABE				30mm ±0.45			
24 OCT 95 Y.ISHIKAWA				24 OCT 95 S.MANABE				角 度 ±3°			
A3 J				LOC				REV. B			
SHEET 1 OF 1				SHEET 1 OF 1				SHEET 1 OF 1			