

Datasheet

## **RS Pro Non-Fused Terminal Block, 12 Way/Pole, Screw Terminals, 4 mm<sup>2</sup> Free Hanging, Panel Mount, PE, 380 V**

RS Stock No: **763-8113**



### **Product Details**

RS Pro non-fused terminal block comes with brass inserts and galvanised steel screws. This easy cut, low cost 12-way polyethylene terminal block operates at a voltage rating of 380 V and temperature rating of +80°C. It supports the wire size of 4 mm<sup>2</sup>.

### **Features and Benefits**

- All screws are captive and raised for easy wiring
- Comes in natural colour
- Temperature rating of +80°C

**Specifications:**

|                               |                           |
|-------------------------------|---------------------------|
| Contact Material              | Brass                     |
| Current Rating                | 3 to 24 A                 |
| Material                      | PE Housing                |
| Maximum Operating Temperature | +80°C                     |
| Mounting Type                 | Free Hanging, Panel Mount |
| Number of Ways                | 12                        |
| Pitch                         | 8 mm                      |
| Termination Method            | Screw                     |
| Voltage Rating                | 380 V                     |
| Wire Size                     | 4 mm <sup>2</sup>         |
| Colour                        | Natural                   |
| Dimensions                    | 93 x 16.8 x 13.6 mm       |
| Standards Met                 | RoHS, CE                  |