




1,6

0,3 MAX.
CUT OFF

3,8

7,6

Ø1,5

3,2

OPTIONAL
SHAPE OF
CARRIERSTRIP

9,9

14,6

Ø1,0

ZONE I

Ø2,2 MAX.

BLUE COLOR CODE
(LOOSE-PIECE ONLY)

WIRE RANGE: 24-28 AWG(0,08-0,22mm²)

INSUL. RANGE: 0,76 - 1,02 mm DIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0,127

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN
-

CHK
K. MALCZYK

APVD
T. DE BOER

PRODUCT SPEC
108-40005

APPLICATION SPEC
114-10000

WEIGHT
-

CUSTOMER DRAWING

5

166294-1

FINISH
LOOSE PIECE

5-166054-1

PART NUMBER

2

166054-1

PART NUMBER

1

TE Connectivity

PIN CONTACT,
SIZE 20 DF.

-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-166054

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
Y

1470-19 (3/11)