

Datasheet

LED Indicator Lamp

ENGLISH

RS ITEM NO 205-410



| | | | | | |
|------------------|---------------|--------------------------|----------------------|-----------|---------------|
| LED/Multiled | <i>Led</i> | Optimum voltage (V) | <i>24Vdc</i> | Intensity | <i>110mcd</i> |
| Mounting Size | - | Rectifier | - | | |
| Mounting Finish | <i>Bi-Pin</i> | AC current | - | | |
| Protection | - | DC current | <i>13mA</i> | | |
| Mount Holder | <i>Bi-Pin</i> | Voltage Tolerance(%) | <i>10%</i> | | |
| Chip Qty | <i>1</i> | Optimum temperature (°C) | <i>-25°C...+60°C</i> | | |
| Indicator colour | <i>Yellow</i> | Storage temperature (°C) | <i>-25°C...+60°C</i> | | |
| Wavelength (nm) | <i>592</i> | Contact Tab | <i>Pin x 2</i> | | |



Dimension in mm (typical), not to scale.
We reserve the right to make changes without further notice to this product to improve reliability, function or design