

Crimping pliers - CRIMPFOX-CX 5,41-M - 1212712

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, compact pliers, coaxial connectors, 0.7 mm, 1.07 mm, 1.69 mm, 3.25 mm, 4.52 mm, 5.41 mm, six marked die stations, unlockable pressure lock, lateral entry, hex crimp

The figure shows a version of the article

Why buy this product

- Crimping pliers for processing coaxial connectors
- Unlockable pressure lock
- Lateral conductor entry



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 857611
Weight per Piece (excluding packing)	618.3 g
Custom tariff number	82032000
Country of origin	Sweden
Note	Made to Order (non-returnable)

Technical data

General

Compression	HEX crimp
-------------	-----------

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811

Crimping pliers - CRIMPFOX-CX 5,41-M - 1212712

Classifications

eCl@ss

eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518