

**SNAP-OFF KNIVES**



**25MM SNAP-OFF KNIFE WITH DYNAGRIP®**

25mm / 1" snap-off blades to help resist snapping and durability. Thumb dial blade release for easy blade change. Eight segments with eight shape tips. Rubber DynaGrip® panels for secure, comfortable grip. Yellow ABS plastic body.

Product ID No.	—Handle Length—		Box/Ctn
	Inches	mm	
10-425			6 / 72



**9MM AND 18MM QUICK-POINT™ KNIVES**

Retractable knife with Quick-Point™ snap-off blades. For light duty cutting and trimming. Blade sections snap-off providing the user with fresh, sharp cutting points. Removable blade snapper included in cap of knife. Supplied with one Quick-Point™ blade. Pocket clip included on 10-150 9mm Quick-Point™ Snap-Off Knife.

Product ID No.	Number of Blades	—Handle Length—		Box/Ctn
		Inches	mm	
10-150	1	5-1/8	130	6 / 72



**9MM EXTRA HEAVY DUTY KNIFE**

Small and sleek design is great for precision cutting. Die cast metal body for durability. The blade slide automatically locks into cutting position. Clamping dial and interlocking nose locks the blade into position. Supplied with one 11-300 blade (equals 13 points).

Product ID No.	—Handle Length—		Box/Ctn
	Inches	mm	
10-095	7-1/4	184	12 / 72



**9MM AND 18MM CUTTERS**

Retractable cutter with quick-point snap-off blades. For light duty cutting and trimming. Blade sections snaps off providing the user with a fresh, sharp cutting point. Supplied with one Quick-Point™ blade. Pocket clip included on 10-131 9mm Pocket Cutter.

Product ID No.	Number of Blades	—Handle Length—		Box/Ctn
		Inches	mm	
10-131P	1	5-3/8	137	60 / 360
10-143P	1	6	152	30 / 180



**DYNAGRIP® 18MM SNAP-OFF CARTRIDGE KNIFE**

Features a blade cartridge which rapidly and automatically slides a new blade into position after old blade is removed. Cartridge dispenser is made from stainless steel to resist rust. Ergonomically designed for comfort and cutting power. The smooth slider mechanism features an audible "click stop" and is self locking for security. Strong and durable tri-material construction. Featuring soft-grip panels for secure grip. Hang hole for storage and lanyard. Blade capacity of six heavy duty or five extra heavy duty blades. Supplied with four 11-301 Heavy Duty blades (equals 32 points).

Product ID No.	Number of Blades	—Handle Length—		Box/Ctn
		Inches	mm	
10-480	4	6-3/4	170	6 / 36



10-131

10-143

QUICK-POINT™ CUTTERS COME IN CONVENIENT COUNTER TOP MERCHANDISERS.



WARNING: Knives are intended for cutting only and should be handled with care. Bending blade can cause it to break, possibly resulting in bodily injury.