

Protective covers - HC-B 10-SD-ML/FS - 1678295


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON protective cover, type B10, for sleeve housing without single locking latch, with retaining cord, IP54



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 151836
Weight per Piece (excluding packing)	48.8 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Diameter of retaining cord eyelet	30 mm
-----------------------------------	-------

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C

General

Type	B10
	For sleeve housing without single locking latch
Material	PA
Seal material	NBR
Locking latch material	High-grade steel, handle: PA-GF
Inflammability class according to UL 94	HB
Seal present	Yes
Connection	Plastic protective cover for short-term protection

Protective covers - HC-B 10-SD-ML/FS - 1678295

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440208

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC002314

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Protective covers - HC-B 10-SD-ML/FS - 1678295

Dimensioned
drawing

Dimensional
drawing

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>