






PRINT DIST

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

METRIC

NUMBER C-172777

3rd ANGLE PROJECTION



注:

1. 適合相手リセプタクル型番 172773, 172774
 2. 製品規格 No. 108-5166
 3. 取付適用規格 114-5072
 4. 相手ハウジング型番 172518 他
- △ 逆巻きリール

NOTES:

1. MATE TAB P/N 172773, 172774
 2. PRODUCT SPEC. No. 108-5166
 3. APPLICATION SPEC. No. 114-5072
 4. PLUG HSG P/N 172518 ETC.
- △ REVERSE REEL

172778-1	錫メッキ済 (PRE-TIN)	黄銅 (BRASS)	△1-172777-1	4
172778-4	錫メッキ済 (PRE-TIN)	黄銅 (PHOS BR)	172777-4	3
172778-2	金メッキ (SELECTIVE GOLD)	黄銅 (BRASS)	172777-2	2
172778-1	錫メッキ済 (PRE-TIN)	黄銅 (BRASS)	172777-1	1
タブ端子型番 (LP NO.)	仕上 (FINISH)	材料 (MATERIAL)	型番 (P/N)	項目 (ID)

© 19 BY AMP (Japan) LTD.
ALL RIGHTS RESERVED.
AMP PRODUCTS COVERED BY PATENTS
AND OR PATENTS PENDING

AMP

AMP (JAPAN), LTD.
Tokyo, Japan

				(P.N)				(MATERIAL)				(FINISH)				(LP NO.)											
				© 19 BY AMP (Japan) LTD. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND OR PATENTS PENDING								AMP				AMP (JAPAN), LTD. Tokyo, Japan											
				WIRE RANGE 0.5~2.27 mm ² (AWG#20~#14)				INSULATION DIA 2.2~3.4 mm				NAME タブコンタクト マルチインターコネクタ (MIC) マーク II TAB MIC MK II															
				MATERIAL 表参照 SEE TABLE				FINISH 表参照 SEE TABLE				GENERAL TOLERANCE 0<≦ 10 : ±0.2 10<≦ 30 : ±0.25 30<≦ 100 : ±0.3 ANGLES : ±3°				SIZE B		LOC J		NUMBER C-172777							
J-10629				DR. H. B. Tanaka 3/19/84				DE. H. B. Tanaka 3/19/84																			
C REDRAWN W/CHANGE				CHK. B. J. Tanaka 3/19/84				APP. B. J. Tanaka 3/19/84																			
LTR REVISION RECORD				DR				CHK				DATE				SCALE 5-1				REV. C				SHEET 1 OF 1			

CUSTOMER DRAWING