

Cam rollers



Dimensions			Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	dynamic C	static C ₀	P _u	dynamic F _r	static F _{0r}			
mm			kN		kN	kN		r/min	kg	-
47	17	17,5	13,8	7,65	0,325	9,5	13,4	8000	0,16	305803 C-2Z

