



Sample photo

Order symbol: PCM 175/100 T
Product nbr: 6016921

Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074038296
El. number:
Finland 3421671
Denmark 8212027255
Italy 7342065
Sweden 2535439

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:		180	180	100	Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 08 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 94 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
inch:		7.1	7.1	3.9	
Materials:					
Material:		PC			Certificates: Germanischer Lloyd (GL) Underwriters Laboratories Det Norske Veritas Fimko Europe EN 50298 1998 UL Canada Gost R
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Cover screws material:		Polyamide			
Cover screws colour:		Black			
Gasket material:		TPE			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MIV 175		Mounting plate			
MIN 15		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP A 175/180		Front plate			
HFP 180		Front plate hinge series			

