

34 - Metric 15° and 75° hinged "midget" open end wrenches | 34.7



Standards

NF ISO 3318, NF ISO 691, ISO 3318, ISO 691, DIN ISO 691

Description

- "Midget" open end wrenches: short shank and slim heads for manoeuvrability in confined spaces.
- Heads hinged at 15° and 75° allow to intervene on nuts inaccessible with a standard wrench.
- Metric sizes: 3.2 to 17 mm.
- Presentation: satin chrome finish.

Specifications

Reference	34.7
[g]	15
L [mm]	80
E [mm]	2,7
B [mm]	15
E maxi [mm]	2,7
A [mm]	7
Width I [mm]	80

