

# A perfect mix of fun and expression



MX 375, CX 175, OMX 185

 **SENNHEISER**



Strut out on the streets in style with your favourite tracks available on demand. With this new range of products from Sennheiser, you will never feel dull again. Thanks to their high-powered dynamic speaker systems, you will enjoy a rich full sonic reproduction. These are complemented with trendy and fashionable designs, made to suit every lifestyle taste. The MX 375, CX 175 and OMX 185 will transform your listening experience into one of indulgence.

- Powerful bass-driven stereo sound
- Highly aesthetic
- Ultra lightweight and ergonomically designed for an optimum fit and comfort
- Optimised for MP3, iPad, iPod, iPhone (iPad, iPhone and iPod are trademarks of Apple Inc., registered in the U.S. and other countries.) and portable media players
- 2 year warranty

## Technical Data

|                                                            | MX 375                                                       | CX 175                                           | OMX 185                                   |
|------------------------------------------------------------|--------------------------------------------------------------|--------------------------------------------------|-------------------------------------------|
| <b>EAN</b>                                                 | 4044155074062                                                | 4044155074208                                    | 4044155074000                             |
| <b>UPC</b>                                                 | 615104221888                                                 | 615104222199                                     | 615104221765                              |
| <b>Article no</b>                                          | 505406                                                       | 505420                                           | 505400                                    |
| <b>Transducer principle</b>                                | Dynamic                                                      | Dynamic                                          | Dynamic                                   |
| <b>Ear coupling</b>                                        | Intraaural                                                   | Intraaural                                       | Intraaural                                |
| <b>Frequency response</b>                                  | 18–22,000 Hz                                                 | 17–23,000 Hz                                     | 18–22,000 Hz                              |
| <b>Impedance</b>                                           | 32 Ω                                                         | 16 Ω                                             | 32 Ω                                      |
| <b>THD – Total harmonic distortion (1 kHz, 100 dB SPL)</b> | < 1 %                                                        | < 1 %                                            | < 1 %                                     |
| <b>Sound pressure level (SPL)</b>                          | 122 dB                                                       | 121 dB                                           | 122 dB                                    |
| <b>Cable length</b>                                        | 1.2 m symmetrical cable                                      | 1.2 m symmetrical cable                          | 1.2 m symmetrical cable                   |
| <b>Jack Plug</b>                                           | 3.5 mm angled plug                                           | 3.5 mm angled plug                               | 3.5 mm angled plug                        |
| <b>Content of delivery</b>                                 | MX 375 earphones, earpads, storage pouch                     | CX 175 ear canal phones, ear adapter set (S/M/L) | OMX 185 earphones, earpads, storage pouch |
| <b>Packaging</b>                                           |                                                              |                                                  |                                           |
| <b>Dimension of product packaging (W x D x H)</b>          | 50 x 37 x 175 mm                                             | 50 x 30 x 175 mm                                 | 100 x 37 x 175 mm                         |
| <b>Weight of earphones and packaging</b>                   | 63 g                                                         | 46 g                                             | 105 g                                     |
| <b>Dimensions of inner master carton (W x D x H)</b>       | 250 x 180 x 58 mm                                            | 208 x 180 x 58 mm                                | 250 x 180 x 108 mm                        |
| <b>Amount of products in inner master carton</b>           | 6                                                            | 6                                                | 6                                         |
| <b>Total weight of inner master carton and products</b>    | 505 g                                                        | 390 g                                            | 776 g                                     |
| <b>Dimension of outer master carton (W x D x H)</b>        | 381 x 255 x 147 mm                                           | 381 x 213 x 147 mm                               | 381 x 263 x 207 mm                        |
| <b>Amount of products per outer master carton</b>          | 24                                                           | 24                                               | 24                                        |
| <b>Total weight of outer master carton and products</b>    | 2391 g                                                       | 1875 g                                           | 3576 g                                    |
| <b>Languages on packaging</b>                              | English, German, French, Spanish, Italian, Dutch, Portuguese |                                                  |                                           |

The publication data was updated to „01/12“.