

Datasheet

Stock No: 399-0754

RS Pro PUR 5000mm Long transparent Flexible Ducting Reinforced, 16mm Bend Radius , Applications Various



Product Details

Flexible Ducting (Zinc plated helix)

An RS Pro polyurethane (PU) hosing with a galvanised steel spiral. Designed to be self-extinguishing and can be used for suction and the transport of dusts, chips and abrasive materials.

Zinc plated spring-steel spiral helix between two layers of crystal clear polyurethane

Highly flexible with excellent internal and external abrasion resistance

May also be used in foundry, general industrial and agricultural applications

Temperature range -40 to +90°C

Note

All data refers to performance at 18°C. Any changes in temperature will affect the performance data

Specifications:

Inner Diameter	63mm
Outer Diameter	68mm
Material	PUR
Length	5000mm
Suitable Applications	Agriculture, Foundry, Industrial
Colour	Transparent
Bend Radius	16mm
Reinforced	Yes