



Search This Product Catalog

[Product Catalog for Global Telecommunications OEM Site](#) > [Products for Equipment Manufacturers](#) > [Products for Mobile/Wireless Equipment Manufacturers](#) > [Board to Board Connectors](#) > [Shunts](#) > [3M™ .100" Shunt Midgie, 929 Series](#) >

 [Printer-friendly format](#) **3M™ .100" Shunt Midgie, 929957-08**
Color plating options 30µ" gray/gold



[\[click to enlarge\]](#)

3M Id : 80-6200-8267-9
GTIN(UPC/EAN) : 0 00 54007 85132 5

Additional Information

- Unique C-Spring contact insures balanced forces.
- Compatible with .025" pins.
- Stackable end-to-end and side-to-side. Color coded for easy identification

Learn More . . .

[Packaging Data](#)
[3M™ .100 in. Shunt, .100" Midgie, 929 Series, TS0200 - Data Sheet \(PDF 369.5 K\)](#)

Please Note:
Adobe® Acrobat® Reader is required to view PDF documents.



Return to Solutions for Network Equipment Manufacturers

- Product Catalog for Global Telecommunications OEM Site
 - Products for Business Enterprise
 - Products for Carriers
 - Products for Equipment Manufacturers

Related Solution Sites

- 3M Access Network
- Enterprise Networks

Characteristics

Contact Material	Copper Alloy
Contact Underplating	50 µ" [1.27 µm] Nickel
Contact Wiping Area Plating	30 µ" [0.76 µm] Gold
Current Rating	1 Ampere
Insulation Color	Gray
Insulation Flammability Rating	UL 94V-0
Insulation Material	Glass Filled Polyester (PBT)
Insulation Resistance	>5 X 109 Ohms @ 500 Vdc
Interface Grid	.100"
Interface Style	Rectangular Socket
Markings	3M Logo
Non-Operating Temperature	-55 to 100 Degree Celsius
Primary Trademark Name	Metpak
Separable	Yes
Termination Style	Shunted Contacts

