

7/8" MALE 90° FIELD-WIREABLE SCREW


5-pol. clamp section 6-8,7mm



Male 90°
5-pole
Screw terminals

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Male





Product may differ from Image

Approvals



Form

78141

Technical Data

Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 9 A
Connection cross section	max. 1.5 mm ²
Sealing range (cable diameter)	6...8 mm
Locking of ports	Screw thread 7/8" (recommended torque 1.5 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

General data

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 11/14

Temperature range -25...+85 °C

Commercial data

country of origin DE

customs tariff number 85369010

minimum order quantity 1