

# Datasheet

# Stainless Steel Toggle Latch, 80kgf OP. Tension

RS Stock number [264-5166](#)



## Description:

This low profile latch is operated by lifting and turning the 'butterfly' thumbscrew, which operates a cam, pulling down the link

The latch can be used with the catch plate supplied, or can grip directly into a groove

The thumbscrew is spring loaded to ensure that it always lies flat

M4 Fixing

80kgf operating tension

Latch to catch distance 32.7mm

## Features:

- Dimensions 43 x 38 x 15mm
- Length 43mm
- Material Stainless Steel
- Operating Tension 80kgf
- Spring Loaded Yes

