

**ENCAPSULATED POWER SUPPLY MODEL 7214**

**INPUT:**

230v nominal (210 – 250v) 50/60Hz

**OUTPUT:**

Voltage:	12V $\pm$ 5% off load
Current:	0.5A max
Load Regulation:	0.5%
Line Regulation:	0.5%
Ripple and noise:	<2mV rms

**PROTECTION:**

Short circuit protected  
Thermal protection

**SAFETY:**

EN60950 – input/output isolation 3.75Kv rms

**OPERATING TEMPERATURE:**

0 – 40c ambient (de-rate output current linearly to 20% at 70c)

**WEIGHT:**

0.5Kg