



# 7DN

## LIMIT SWITCH LEVER MS+ML +OPTIONS



Download your 7DN datasheet



Characteristics | Documents & Downloads

### Main Hide

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007MS04.. 9007ML04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return adjustable roller lever length: 1.38...3.38 in -
Type of roller	1 nylon outside roller diameter: 0.75 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

### Complementary Hide

Tracks	1.50 in
Switch actuation	By 30° cam
Product weight	0.1 lb(US)

### Environment Hide

Ambient air temperature for operation	-40...221 °F
Ambient air temperature for storage	-40...221 °F
Environmental characteristic	Standard environment

### Offer Sustainability Hide

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be Compliant on 3Q2014 Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">download Product environmental</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty Hide

Period	18 months
--------	-----------