

DIN-Power H015FS4,0C1-1 (NFF)



Image is for illustration purposes only.
Please refer to product description.

Part number:	09 06 215 2821 222
Description:	DIN-Power H015FS4,0C1-1 (NFF)
Termination length:	4.0 mm
Application:	Power Backplane-to-Daughtercard
Combination:	Mezzanine Cable to Board
No. of contacts:	15
Performance level:	PL 1 acc. to IEC 60603-2
pcb fixing:	without snap in clips
Quality-Level:	premium standard
Railway classification:	F1/I2 acc. to NFF 16-101
Contact Pitch:	10.16 mm
Series:	DIN 41612
Current:	15 A @ 20°C
contact orientation:	straight
Gender:	Female
Plastic features:	CTI < 400
Type:	H
Termination Type:	Solder
Flange:	with Flange
Mating face:	DIN type H15
RoHS conformity:	Yes