


DO NOT SCALE

DIMENSIONS IN mm

METRIC




THIRD ANGLE

PROJECTION




NOTES

- ① SNAP-IN POLARIZERS PN. 927636-2 OR 927637-2 CAN BE APPLIED.
- ② THERE IS NO WINDOW FOR SNAP-IN POLARIZERS AT THIS END IN 10 AND 14 POS. HEADERS.
- ③ INDICATION OF FIRST POSITION.
- ④ THERE IS NO CENTER STAND-OFF IN 10-26 POS. HEADERS.
- ⑤ PARTNUMBER AND PROD.-DATE ON SUITABLE SURFACE X-828 586-X
DD.MM.YY



RECOMMENDED PCB-HOLE PATTERN



② PIN-CONTACT

BRASS

MATING SIDE: 0,8µm AU
OR 0,8µm AMP DURAGOLD®/
OVER 1,27µm NI
SOLDER SIDE: MIN. 3,0µm SN
OVER 1,27µm NI

① HOUSING

GLASSFILLED POLYESTER

GREY

100,6	90,4	96,5	86,4	78,7	64	6-828586-4
95,5	85,3	91,4	81,3	73,7	60	6-828586-0
82,8	72,6	78,7	68,6	61,0	50	5-828586-0
70,1	59,9	66,0	55,9	48,3	40	4-828586-0
62,5	52,3	58,4	48,3	40,6	34	3-828586-4
52,3	42,2	48,3	38,1	30,5	26	2-828586-6
44,7	34,5	40,6	30,5	22,9	20	2-828586-0
39,6	29,5	35,6	25,4	17,8	16	1-828586-6
37,1	26,9	33,0	22,9	15,2	14	1-828586-4
32,0	21,8	27,9	17,8	10,2	10	1-828586-0
DIM. "E"	DIM. "D"	DIM. "C"	DIM. "B"	DIM. "A"	NR. OF POSITIONS	PARTNUMBER
VARIABLE CONNECTOR DIMENSIONS						

COMPONENT NAME

MATERIAL

PLATING/COLOUR

CUSTOMER DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19- BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.

THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION - ,19 -

AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

NAME
AMP-LATCH HEADER 90° VERSION
WITH LATCHES

DR.: J.v.LIEMPT

CHK.: R.VERSTIJNEN

APP.: L.v.SOEST

DWG.No. C-828586

LOC. AI

A3

SHEET 1 OF 1

REV.LTR. A1

DATE: 29-11-93

DATE: -

DATE: -