

Amphenol 4 Way Panel Mount XLR Connector, Female, Silver Plated Contacts

RS Stock No: 666-0601



Product Details

AC Z Series D Type Chassis Connectors

D size housing can be front or rear mounted using the same panel cutout
 Solder bucket connections
 Leading first mate last break socket contact
 Positive latch lock system
 Vertical PCB mounting (not available in 4 contact female)

Amphenol XLR Connectors

General Specifications:

Number of Contacts	4
Gender	Female
Mounting Type	Panel Mount
Body Orientation	Straight
Contact Plating	Silver
Housing Material	Zinc Alloy
Termination Method	Solder
Current Rating	10A
Contact Material	Brass
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+75°C