

## Datasheet

# RS Pro 12 Way Commoning Block, Screw Down Termination, 10 to 5 AWG, 16 mm<sup>2</sup>, 6 mm<sup>2</sup> CSA, Clear, 100A 450 V

RS Stock No: **388-2855**



## Product Details

RS Pro 26-way terminal block for earth bonding applications, is supplied complete with accessories for DIN rail mounting. This terminal block is compact and provides a connection system on two levels which allows easy insertion of conductors. The brass connection bars are nickel plated for protection against corrosion and are contained within a transparent blue PC housing. The use of this terminal block is recommended for potential equalisation providing additional protection to earth (ground) for medical equipment.

## Features and Benefits

- Housing material: PC, blue transparent
- Self extinguishing: UL 94 - V0; IEC 695-2-1 IEC 695-2-2
- Maximum operating temperature: 85°C
- Clamps: Brass nickel plated
- Screws: Galvanised steel, Phillips + slotted head

**Specifications:**

Cable CSA	16 mm <sup>2</sup> , 6 mm <sup>2</sup>
Colour	Clear
Current Rating	100 A
Height	36.5 mm
Length	104.5 mm
Maximum Operating Temperature	+85°C
Number of Ways	12
Termination Method	Screw Down
Voltage Rating	450 V
Width	32.5 mm
Wire Size	10 to 5 AWG
Body Material	PC