

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE interface module for Siemens SIMATIC® S7-300, for max. 16 channels with SIMATIC®-specific labeling (1 - 20), with screw connection, module width: 80.6 mm



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 313070
Weight per Piece (excluding packing)	150.4 g
Custom tariff number	85369010
Country of origin	United States

### Technical data

#### Dimensions

Width	80.6 mm
Height	65.5 mm
Depth	56 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Nominal voltage $U_N$	60 V AC/DC
Max. current carrying capacity per branch	1 A
Number of positions	14
Status display	No
Mounting position	any
Standards/regulations	IEC 60664
	DIN EN 50178

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Technical data

#### General

	IEC 62103
Pollution degree	2
Surge voltage category	II
Rated surge voltage	0.6 kV

#### Connection data for connection 1

Connection name	Field level
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M 3

#### Connection data for connection 2

Connection name	Control system level
Number of connections	2
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	14

#### Supported controller

Control	GE-FANUC 90-30
- suitable I/O card	IC693 MDL732
	IC693 MDL733
	IC693 MDL740
	IC693 MDL741
	IC693 MDL742
	IC693 ALG220
	IC693 ALG221
	IC693 ALG222
	IC693 ALG223
	IC693 ALG390
	IC693 ALG391
	IC693 ALG392
	IC693 ALG442

# Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC001604

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Approvals

### Approvals

#### Approvals

CSA / UL Recognized / cUL Recognized / UL Recognized / cULus Recognized

#### Ex Approvals

#### Approvals submitted

### Approval details

CSA	
mm <sup>2</sup> /AWG/kcmil	30-12

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Approvals

Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

UL Recognized

mm <sup>2</sup> /AWG/kcmil	30-12
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

cUL Recognized

mm <sup>2</sup> /AWG/kcmil	30-12
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

UL Recognized

mm <sup>2</sup> /AWG/kcmil	30-12
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

cULus Recognized

### Accessories

Accessories

System cable

Cable - FLK 14/EZ-DR/ 30/KONFEK - 2295729



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 0.3 m

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Accessories

Cable - FLK 14/EZ-DR/ 50/KONFEK - 2288901



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 0.5 m

---

Cable - FLK 14/EZ-DR/ 100/KONFEK - 2288914



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 1 m

---

Cable - FLK 14/EZ-DR/ 150/KONFEK - 2288927



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 1.5 m

---

Cable - FLK 14/EZ-DR/ 200/KONFEK - 2288930



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 2 m

---

Cable - FLK 14/EZ-DR/ 250/KONFEK - 2288943



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 2.5 m

---

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Accessories

Cable - FLK 14/EZ-DR/ 300/KONFEK - 2288956



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 3 m

---

Cable - FLK 14/EZ-DR/ 350/KONFEK - 2288969



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 3.5 m

---

Cable - FLK 14/EZ-DR/ 400/KONFEK - 2288972



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 4 m

---

Cable - FLK 14/EZ-DR/ 450/KONFEK - 2290847



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 4,5 m

---

Cable - FLK 14/EZ-DR/ 500/KONFEK - 2290834



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 5 m

---

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Accessories

Cable - FLK 14/EZ-DR/ 550/KONFEK - 2290850



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 5,5 m

---

Cable - FLK 14/EZ-DR/ 600/KONFEK - 2290863



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 6 m

---

Cable - FLK 14/EZ-DR/ 800/KONFEK - 2299563



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 8 m

---

Cable - FLK 14/EZ-DR/1000/KONFEK - 2299576



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 10 m

---

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

---

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Accessories

Cable - FLK 14/EZ-DR/ 50/KONFEK/S - 2296977



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 0.5 m

---

Cable - FLK 14/EZ-DR/ 100/KONFEK/S - 2296980



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 1 m

---

Cable - FLK 14/EZ-DR/ 200/KONFEK/S - 2297002



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 2 m

---

Cable - FLK 14/EZ-DR/ 300/KONFEK/S - 2299013



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 3 m

---

Cable - FLK 14/EZ-DR/ 400/KONFEK/S - 2299026



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 4 m

---

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Accessories

Cable - FLK 14/EZ-DR/ 600/KONFEK/S - 2299039



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 6 m

---

Cable - FLK 14/EZ-DR/ 800/KONFEK/S - 2299042



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 8 m

---

Cable - FLK 14/EZ-DR/1000/KONFEK/S - 2299055



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 10 m

---

Cable - FLK EZ-DR-S.../.../... - 2295046



Round cable, with preassembly, shielded, variable cable length

---

Cable - FLK 14/EZ-DR/HF/ 50/KONFEK - 2305952



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable. Length of cable: 0.5 m

---

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Accessories

Cable - FLK 14/EZ-DR/HF/ 100/KONFEK - 2305965



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable. Length of cable: 1 m

---

Cable - FLK 14/EZ-DR/HF/ 150/KONFEK - 2305978



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable. Length of cable: 1.5 m

---

Cable - FLK 14/EZ-DR/HF/ 200/KONFEK - 2305981



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable. Length of cable: 2 m

---

Cable - FLK 14/EZ-DR/HF/ 250/KONFEK - 2305994



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable. Length of cable: 2.5 m

---

Cable - FLK 14/EZ-DR/HF/ 300/KONFEK - 2304759



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable. Length of cable: 3 m

---

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Accessories

#### Cable - FLK 14/EZ-DR/HF/ 400/KONFEK - 2304762



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable.  
Length of cable: 4 m

---

#### Cable - FLK 14/EZ-DR/HF/ 500/KONFEK - 2304717



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable.  
Length of cable: 5 m

---

#### Cable - FLK 14/EZ-DR/HF/ 600/KONFEK - 2306003



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable.  
Length of cable: 6 m

---

#### Cable - FLK 14/EZ-DR/HF/ 700/KONFEK - 2314011



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable.  
Length of cable: 7 m

---

#### Cable - FLK 14/EZ-DR/HF/ 800/KONFEK - 2314024



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable.  
Length of cable: 8 m

## Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

### Accessories

#### Cable - FLK 14/EZ-DR/HF/1000/KONFEK - 2314037



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable.  
Length of cable: 10 m

---

#### Cable - FLK 14-EZ-DR-HF/... - 2314040



Assembled halogen-free round cable, with two 14-pos. socket strips (1:1 connection), to transfer 8 channels, for example. Halogen-free refers exclusively to the 14-pos. cable.  
Length of cable: Variable

---

### Terminal marking

#### Marker for terminal blocks - UC-TM 4 - 0818111



Marker for terminal blocks, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 4.2 mm, Lettering field: 3.6 x 10.5 mm

---

#### Marker for terminal blocks - UC-TM 6 - 0818085



Marker for terminal blocks, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

---

#### Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793



Zack marker strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 5.08 mm, Lettering field: 4.98 x 10.5 mm

# Passive module - VIP-2/SC/2FLK14 (1-20) /S7 - 2315230

## Accessories


Zack marker strip - ZB 22:UNBEDRUCKT - 0811862



Zack marker strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 22 mm, Lettering field: 10.5 x 21.8 mm

## Drawings

Circuit diagram



Connection diagram: VIP-2/.../2FLK14 (1-20) /S7