



ENGLISH

Datasheet

RS Pro Toggle Switch DPDT On-On-On, 4 A @ 30 V dc, Panel Mount

RS Stock No: **344-710**



Product Details

RS Pro DPDT toggle switch has chrome plated lever for a smooth operation. This panel mount switch performs on-on-on operation. It withstands currents up to 4 A at 30 V dc voltage. The fine silver contacts offer superior performance.

Features and Benefits

- Slow make-and-break action
- Chrome plated lever
- Solder bucket terminals
- Silver contacts
- Maximum load of 0.4 VA
- Glass filled polyester case



ENGLISH

Specifications:

Actuator Length	10.5 mm
Actuator Material	Chrome Plated Brass
Contact Configuration	DPDT
Contact Current Rating	6 A at 250/125 V ac
Contact Material	Silver Plated Copper Alloy
Contact Resistance	10 mΩ
Maximum Operating Temperature	+70°C
Mechanical Life	50000 to 100000 cycles
Minimum Operating Temperature	-20°C
Mounting Type	Panel Mount
Operating Temperature Range	-20 to +70°C
Panel Cut Out Diameter	6.2 mm
Standards Met	CSA Recognised, RoHS Compliant, UL 94V-0 Listed
Switch Operation	On-On- (On)
Terminal Type	Through Hole
Actuator Type	Standard
Bushing Style	Threaded