


Cable tie - WT-HF 7,8X300 - 3240772

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable binders for quick and secure bundling, standard version

Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 704908
Weight per Piece (excluding packing)	4.38 g
Custom tariff number	39269097
Country of origin	Italy

Technical data

Dimensions

Length (b)	300 mm
Width (a)	7.8 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Optimum ambient temperature (storage/transport)	23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.
Short-term temperature	110 °C

General

Color	transparent
Type	Internal teeth
Components	free from silicone and halogen
Inflammability class according to UL 94	V2

Cable tie - WT-HF 7,8X300 - 3240772

Technical data

General

Material	PA 6.6
----------	--------

Classifications

eCl@ss

eCl@ss 4.0	27140702
eCl@ss 4.1	27140702
eCl@ss 5.0	27140702
eCl@ss 5.1	27140702
eCl@ss 6.0	27140702
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702

ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

Approvals

Approvals

Approvals

UL Recognized / LR / GL / BV / DNV / RINA


Ex Approvals

Approvals submitted

Approval details

Cable tie - WT-HF 7,8X300 - 3240772

Approvals

UL Recognized 

LR

GL

BV

DNV

RINA

Accessories

Accessories

Universal tools

Cable tie tool - UNIFOX-CT 4,8 - 1212475



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Cable tie tool - UNIFOX-CT 4,8P - 1212609



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm