

# Specifications for BMP51/53 Labelmaker Tags

<b>Article No.</b>	143220
<b>Brady Material No.</b>	<a href="#">B-109</a>
<b>Material Type</b>	Polyethylene Tag
<b>Colour</b>	Black on White
<b>Finish</b>	Matt
<b>Order Reference</b>	M-12-109
<b>Printable Area - Height (mm)</b>	56.00
<b>Printable Area - Width (mm)</b>	19.05
<b>Printer Compatibility</b>	BMP51; BMP53
<b>Size - Height (mm)</b>	76.20
<b>Size - Width (mm)</b>	19.05
<b>Additional Information</b>	Good cold-weather tag
<b>Thickness (mm)</b>	0.216
<b>Total Qty per Pack</b>	80 Tag(s) / Box
<b>Adhesive (Y/N)</b>	No
<b>Application</b>	Communication Cabling; Power & Ground Cables; Voice & Data Communciation; Wire & Cable Marking
<b>Description</b>	Multi-purpose tag that can be used for a variety of applications including identification of multi-conductor cables, inventory, equipment, lockout, safety warning repair and work-in-progress. Extremely tear resistant and superior cold-weather tag.
<b>Max. Service Temp. °C</b>	49
<b>Min. Service Temp. °C</b>	-40
<b># of Holes</b>	4
<b>Software</b>	LabelMark
<b>Voice/Data Application</b>	Communications Cables;Power & Ground Cables