


NO	DESCRIPTION	DATE
①	⟨ø16.5⟩ → ⟨ø17.0⟩	03.06.96
②	BACKGROUND FORMAT UPDATED	01.04.03
③	MODIFY DESIGN	01.15.04

RS PART NO: 6563620



- NOTES: UNLESS OTHERWISE SPECIFIED
- 1. BODIES:BRASS PER JIS-C3604
 - 2. CENTER CONTACT:BRASS PER JIS-C3604
 - 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
 - 4. CONNECTOR INTERFACE PER MIL-STD-348A
 - 5. PART TO BE CLEAN AND FREE OF BURRS

4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD
2	BODY	BRASS	1	NICKEL 100μ" MIN.
1	CHASSIS	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

 by _____ DATE: _____

DESCRIPTION			N JACK-JACK						
製圖	DRAWN	TOLERANCE		品名	11-21-4/ROHS COMPLIANT (50Ω)	日期	DATE	版次	REV.
	Ruby			TITLE			03.16.92		
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	11-0094		
	Monica								
認定	APPROVAL	.XXX	±0.05	比例	SCALE		佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.		
	Monica								