

Datasheet

RS Pro Trace Heating Thermostat, -40 to 77 °C

RS Stock No: **665-7576**



Product Details

RS Pro trace heating thermostat is suitable for operating temperatures ranging from -40 to +77°C. It is designed for the control of surface temperatures of trace heating pipes and vessels within a hazardous area. It is an on/off unit with electrical switch operated by expansion of the liquid in the sensing bulb or capillary.

Features and Benefits

- -40 to +77°C
- SIRA approved for zone I and zone II hazardous areas
- ATEX certification



Specifications:

Hazardous Area Certification	ATEX
Maximum Operating Temperature	+77°C
Minimum Operating Temperature	-40°C
Operating Temperature Range	-40 to +77°C
Type	Thermostat