



CERTIFICATION RECORD

The company named below has been authorized by CSA to represent the products listed in this record as "CSA Certified" and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

NUMBR 025706W0000 July 31, 1997 (Replaces: July 7, 1995)

CLASS 3211 05 (Re-examination Service)

BACO, CONSTRUCTIONS ELECTRIQUES S.A.
1290 Route de Colmar
B.P. 101F
67024 Strasbourg-Cedex, France

25706

INDUSTRIAL CONTROL EQUIPMENT - Motor Controllers - Manual

- AC Cam-operated rotary controllers, single-phase or polyphase, open type, for flush mounting or back-of-panel mounting, the switching sections being assembled in various combinations as required for reversing, speed control and similar applications, with the following max ratings, 3-phase: PR10, 10A, 4.5 hp, 300V; PR12, 12A, 3 hp, 600V; PR16, 16A, 10 hp, 600V; PR20, 20A, 14 hp, 600V; PR25, 25A, 20 hp, 600V; PR40, 40A, 30 hp, 600V; PR63, 63A, 40 hp, 600V.

Notes:

1. The type designation is completed with letters and numbers indicating the switching combinations, terminals etc.
2. The types PR16 and PR20 may be provided with special additional terminals, then the max rated voltage is reduced to 300V. The assemblies are certified only for use where the acceptability of the combination has been determined by the Canadian Standards Association.

* * * * *