







PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PBT
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT PIN: BRASS (CuZn)
SOLDER TAIL PLATING: TIN

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL	cULus	VDE
CURRENT RATING:	20A	20A
WORKING VOLTAGE:	300VAC	300VAC
WITHSTANDING VOLTAGE:	1.6KV	2.5KV
CONTACT RESISTANCE:	20 mOhm MAX	


STANDARD
ULus CERTIFIED E315414 / MODEL NUMBER 313
RoHS CERTIFIED 40023195 / MODEL NUMBER 313

MECHANICAL
PITCH: 5.08MM

SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 313

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15			
G								
F								
E								
D				APPROVAL: RJ	UNIT: MM	DESCRIPTION: SERIE 313 - 5.08MM CLOSE HORIZONTAL PCB HEADER WR-TBL		SIZE A4
C	13-OCT-09	STANDARD	JP		SCALE:			
B	29-OCT-08	CHARACTERISTICS	JP		SHEET: 1/1	WERI PART NO: 691 313 510 0xx		
A	31-OCT-07	PDF	EC		DRAW: MARVIN			
REV	DATE	FILE	BY					