





REV.	CNN	CNN DESCRIPTION	Date	Check in
03			02/02/2010	Shaun Barron



ELECTRICAL SPECIFICATION

RATED VOLTAGE	250V
RATED CURRENT	10A @40°C
FREQUENCY	50/60Hz
TEMPERATURE RANGE	-25° TO +85°C
EARTH LEAKAGE CURRENT	<0.35mA @230V 50Hz
TEST VOLTAGE	2.1kV dc
TERMINATIONS:	
EN60320 (IEC320) APPLIANCE INLET	
EN60320 (IEC320) APPLIANCE OUTLET	
METAL OXIDE VARISTORS	L - N 275V

RoHS
2002/95/EC
Compliant

Tel No.+44(0)1724273200 Website www.dem-uk.com

Alpha3
manufacturing

ROXBURGH EMC

DELTRON Components

DELTRON Enclosures

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
ALPHA 3 MANUFACTURING.
ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN
PERMISSION OF
ALPHA 3 MANUFACTURING IS PROHIBITED.

DEM

DEM Manufacturing, Deltron Emcon House
Hargreaves Way, Sawcliffe Ind. Park,
Scunthorpe, North Lincolnshire, DN15 8RF, UK

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETRES
LINEAR TOLERANCE:
NO DECIMAL PLACES ±0.5mm
1 DECIMAL PLACE ±0.25mm
2 DECIMAL PLACES ±0.125mm
ANGULAR TOLERANCE: ±1°

FINISH

DEBURR AND
BREAK SHARP
EDGES

DRAWN BY

APPROVED BY

SW

BS

TITLE

GENERAL SPECIFICATION
250V 10A 50/60Hz
PORTABLE MAINS FILTER

DRAWING NO.

PMF10

ISSUE

03

Release

IF IN DOUBT ASK
DO NOT SCALE DRAWING



SHEET 1 OF 1

SCALE 2:3

A3

MATERIAL