

NO	DESCRIPTION	DATE
①	WORKING VOLTAGE → VOLTAGE RATING DEL PROOF VOLTAGE	09.15.15'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-11 GHz
1.2 NOMINAL IMPEDANCE: 50 OHMS
1.3 VOLTAGE RATING: 1000 VOLTS MAX. 
1.4 VSWR: 1.1 MAX. @6 GHz
1.3 MAX. @11 GHz

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3804
2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.**

4.0 MECHANICAL

- #### 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C**

5	O-RING	SILICONE	1	BLACK
4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD 3 μ "MIN.
2	BODY	BRASS	1	WHITE BRONZE 80 μ "MIN.
1	CHASSIS	BRASS	1	WHITE BRONZE 80 μ "MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by DATE:



DESCRIPTION			LOW PIM N STRAIGHT BULKHEAD JACK RECEPTACLE									
製圖	DRAWN	TOLERANCE		品名	61-18		T.G.WB		日期	DATE	版次	REV.
	Yoko	X	±0.2	TITLE	R0HS COMPLIANT		(50Ω)			02.16.12'		A-1
檢圖	CHECK	XX	±0.1	單位	UNIT	DWG.NO.		61-0004				
	Arc				mm(In)							
認定	APPROVAL	XXX	±0.05	比例	SCALE							
	Jenny				ANGLE							