







KEY LESS

-2 ONLY



- 注記
- 1 材料: 熱可塑性ポリエステル樹脂
 - 2 色: 黒
 - 3 使用端子: 175194, 175195 または 175196
 - 4 使用端子 (ノズル): 175216, 175217 または 175218
 - 5 製品規格: 108-5349
 - 6 認定評価報告書: 501-5013

- NOTES
- 1 MATERIAL: GLASS FIELD THERMO PLASTIC, POLYESTER.
 - 2 COLOR: BLACK
 - 3 CONT. FOR THIS CONN.: 175194, 175195 AND 175196.
 - 4 CONTACT L/P: 175216, 175217 AND 175218.
 - 5 PRODUCT SPEC: 108-5349
 - 6 QUALIFICATION TEST REPORT: 501-5013

-1, -2; AS SHOWN

Copyright ©1998 年				Copyright ©1998				AMP				日本エー・エム・ピー株式会社			
日本エー・エム・ピー株式会社				AMP (Japan), LTD.								kawasaki, Japan			
絶縁電線断面積 (WIRE RANGE)				絶縁外径 (INSULATION DIA.)				名称 (NAME)				DYNAMIC (D-3500)			
mm ² (AWG -)				mmφ								REC. HSG. 6POS.			
材料 (MATERIAL)				仕上 (FINISH)				一般公差 (GENERAL TOLERANCE)				L/C			
(SEE NOTE)								10mm以下: ±0.2				B J			
注記参照								10mm以上 30mm以下: ±0.25				番号 (No.)			
O RELEASED FJ00-1298-98				DR. 18 SEP 98				DE. 18 SEP 98				1318095			
M.HIGO				M.HIGO											
LTR 変更 (REVISION RECORD)				CHK. 24 SEP 98				APP. 25 SEP 98				尺度 (SCALE)			
DR				CHK. n. matsuoka				APP. J. Hasegawa				2-1			
DATE												REV. 0			
												SHEET 1 OF 1			