



Rampmat

Economical anti-fatigue mat

- A handy and economical anti-fatigue mat for the workplace.
- Raised circular surface for superior slip resistance.
- Conforms to Slip Resistance Test EN13552 Category R10.
- Open drainage holes for spilt liquids.
- Made from hardwearing SBR/NBR rubber.
- Moulded bevelled edges reduce trip hazards.

Product height: 14mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.9 x 1.5	10.65	17.5 x 17.5 x 105	Boxed	1	30	Black	RP010001

Edged all round

Other: Silicone is used in the production process of the mats and a residue will possibly be left on the mat.

Operating Temperature: -20°C to +130°C

End of document

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

+44 (0)116 240 1088
sales@cobaeeurope.com
www.cobaeeurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

+49 (2161) 2945-0
verkauf@cobaeeurope.de
www.cobaeeurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamence 11
SK-013 06

+421 41 507 11 12
sales@cobaeeurope.sk
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.